



Metric table

Dimensions in: millimeters - inches

¹ b	² l ₁	d Thread	l ₂	l ₃	l ₄	l ₅	m	t ₁	t ₂	Radial load	Axial load
15 0.59	63 2.48	M 5	17 0.67	31 1.22	6.1 0.24	10 0.39	19 0.75	5 0.20	10 0.39	2300 N 517 lbf	1500 N 337 lbf

Specification

- Zinc die-cast, powder coated
Black, RAL 9005, textured finish
- Washer
Plastic
- RoHS compliant



Information

GN 161.1 lift-off hinges are a unique variation with a highly attractive design. The mounting screws are concealed.

During load tests, these hinges were gradually loaded and relieved at room temperature with incrementally increasing force.

For the specified values, an insignificant permanent deformation remained after relieving the load which had no effect on the function and appearance. In most cases, the failure loads are multiples of the specified value.

Indicated load bearing capacities are non-binding recommended values and constitute no general warranty of quality and condition. The user must determine from case to case whether a product is suitable for the intended use. Environmental influences and aging may influence these values.

see also...

- List of Hinge Types → page 1324
- Lift-Off Hinges EN 160 → www.jwwinco.com

How to order GN 161.1-15-63-SW	¹ Width b
	² Length l ₁
	³ Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

