



Specification

- Steel, blackened finish
- RoHS compliant

On request

- Different lengths or other material thicknesses available for quantities above 100 pieces

Information

DIN 1810 hook spanner wrenches are used to install and tighten slotted spanner nuts or leveling sets, for example.

see also...

- *Slotted Spanner Nuts DIN 1804* → page QVX
- *Slotted Spanner Nuts DIN 70852* → page QVX
- *Bearing Lock Nuts KM* → page QVX
- *Slotted Spanner Lock Nuts GN 1804.1* → page QVX
- *Slotted Spanner Lock Nuts GN 1804.2* → page QVX
- *Leveling Sets GN 350* → page QVX
- *Leveling Sets GN 350.1* → page QVX
- *Leveling Sets GN 350.2* → page QVX
- *Leveling Sets GN 350.5* → page QVX

How to order

DIN 1810-A34-36

- | | |
|---|--------|
| 1 | d min. |
| 2 | d max. |

Metric table

Dimensions in: millimeters - inches

1 d min.	2 d max.	Length l	b
A 12	14 0.55	110 4.33	3 0.12
A 16	20 0.79	110 4.33	3 0.12
A 25	28 1.10	136 5.35	4 0.16
A 30	32 1.26	136 5.35	4 0.16
A 34	36 1.42	170 6.69	5 0.20
A 40	42 1.65	170 6.69	5 0.20
A 45	50 1.97	206 8.11	6 0.24
A 52	55 2.17	206 8.11	6 0.24
A 58	62 2.44	240 9.45	7 0.28
A 65	70 2.76	240 9.45	7 0.28
A 68	75 2.95	240 9.45	7 0.28
A 80	90 3.54	280 11.02	8 0.31
A 85	92 3.62	280 11.02	8 0.31
A 95	100 3.94	280 11.02	8 0.31
A 98	105 4.13	290 11.42	8 0.31
A 110	115 4.53	335 13.19	10 0.39
A 120	130 5.12	335 13.19	10 0.39
A 135	145 5.71	385 15.16	10 0.39
A 155	165 6.50	385 15.16	10 0.39
A 180	195 7.68	470 18.50	10 0.39
A 205	220 8.66	470 18.50	10 0.39
A 230	245 9.65	568 22.36	10 0.39
A 260	270 10.63	568 22.36	10 0.39
A 280	300 11.81	680 26.77	15 0.59
A 300	320 12.60	695 27.36	15 0.59
A 320	345 13.58	695 27.36	15 0.59
A 350	375 14.76	735 28.94	15 0.59
A 380	400 15.75	770 30.31	15 0.59
A 480	500 19.69	988 38.90	20 0.79

