



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² b	d ₂	s	t	For thread size
22 0.87	6.2 0.24	16 0.63	6 0.24	0.8 0.03	M 6
28 1.10	8.3 0.33	21 0.83	7 0.28	1 0.04	M 8
34 1.34	10.4 0.41	25 0.98	8 0.31	1.2 0.05	M 10
40 1.57	12.5 0.49	30 1.18	9 0.35	1.8 0.07	M 12
56 2.20	16.5 0.65	37 1.46	12 0.47	1.8 0.07	M 16

Specification

- Steel
 - Case-hardened
 - Blackened finish
- RoHS compliant

Information

GN 183 knurled C-washers transfer the clamping force of a screw or nut to the workpiece. They can be pushed out of the clamping point after releasing the screw thread.
The dimensions are almost identical to C-washers DIN 6372.

How to order ¹ ² GN 183-34-10.4	1 Outer diameter d ₁
	2 Inner diameter b

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10