



SS Stainless Steel

**Metric table**

1

Dimensions in: millimeters - inches

$d_1^{+0.2/+0.3}$	$d_2 - 0.5$	$h$	$t$	For GN 187.4 serrated locking plates - $d_0$
22 .87	26 1.02	14.5 .57	12.5 .49	22 .87
27 1.06	31 1.22	16.5 .65	14.5 .57	27 1.06
32 1.26	36 1.42	19.5 .77	17.5 .69	32 1.26
40 1.57	44 1.73	24.5 .96	22.5 .89	40 1.57

**Specification**

- Steel, blackened finish
- Stainless steel AISI 303
- RoHS compliant

2

ST  
NI

**Information**

GN 187.1 guide housings are utilized with GN 187.4 serrated locking plates.

see also...

- Serrated Locking Plates GN 187.4

<p>How to order</p> <p><b>GN 187.1-27-NI</b></p>	1	Inner diameter $d_1$
	2	Material