



SS Stainless Steel

**Metric table**



Dimensions in: millimeters - inches

d	Max. spring load ≈	For GN 187.4 / EN 189 serrated locking plates - d <sub>0</sub>	For GN 187.5 serrated locking plates - d <sub>0</sub>
15 .59	20 N 4.50 lbf	22 .87	-
18 .71	35 N 7.87 lbf	27 1.06	27 1.06
23 .91	55 N 12.36 lbf	32 1.26	32 1.26
29 1.14	45 N 10.12 lbf	40 1.57	40 1.57

**Specification**

- Stainless steel AISI 301
- RoHS compliant

**Information**

GN 187.2 conical thrust springs are placed between GN 187.4 / EN 189 / GN 187.5 serrated locking plates to ensure that the locking plates separate reliably when removed.

see also...

- Serrated Locking Plates GN 187.4 (Steel / Stainless Steel)
- Serrated Locking Plates EN 189 (Plastic)
- Serrated Locking Plates GN 187.5 (Stainless Steel)

How to order



**GN 187.2-18**

1 Outer diameter d

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10