



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² Length l ±0.25	d ₂	h
8 .31	30 1.18	12 .47	26 1.02
10 .39	40 1.57	15 .59	31 1.22

Specification

- **GN 224.1**
Steel, chrome-plated finish CR
Location disks
Zinc die-cast, nickel-plated finish
- **GN 224.5**
Stainless steel
European Standard No. 1.4301 (AISI 304),
matte shot-blasted finish
Location disks
Stainless steel
European Standard No. 1.4305 (AISI 303)
- **RoHS compliant**

Information

GN 224.1 and GN 224.5 finger grip handles are supplied with two location disks. They guarantee a perfect location even with oversize mounting holes in the cabinet. The disks are supplied loose.

On request

- Various metric size fasteners and kit packaging

How to order (Steel) ¹ ² ³ GN 224.1-8-30-CR	1 Handle diameter d ₁
	2 Length l
	3 Finish
How to order (Stainless steel) ¹ ² GN 224.5-10-40	1 Handle diameter d ₁
	2 Length l