



ELESA original design MFH



Metric table

1 d ₁	2 Length l		3 d ₂ Bore	d ₃	h
	Nominal dimension	Actual dimension			
9 .35	30 1.18	29.5 1.16	B 3.5	12 .47	27 1.06
10 .39	40 1.57	39.5 1.56	B 3.5	15 .59	33.5 1.32

Dimensions in: millimeters - inches

Specification

- Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to 212 °F (100 °C)
- Color (matte finish):
 - SW
 - OR
 - GR
 - RT
 - CL
- RoHS compliant

Information

EN 224.3 finger grip handles with bore hole B 3.5 mm are intended for mounting with self-tapping screws, such as DIN ISO 7049 pan head tapping screws of thread size ST 4.2 mm.

see also...

- Product Range Cleanline
- Finger Grip Handles GN 224.1 (Steel)
- Finger Grip Handles GN 224.5 (Stainless Steel)

How to order	
1	Handle diameter d ₁
2	Length l
3	Bore d ₂
4	Color

1
2
3
4
EN 224.3-10-40-B3.5-SW