



4 Sensitivity
30 Angular minutes,
bubble moves by 2 mm

Metric table

2

Dimensions in: millimeters - inches

d_1	d_2	d_3	d_4 Thread	h_1	h_2	t
17 .67	12 .51	13.2 .47	M 3	13 .51	14.7 .57	5 .20
20 .79	14 .51	13 .55	M 3	14.5 .59	17 .67	5 .20
24 .94	16 .59	15 .63	M 3	17 .67	20 .79	5 .20

Specification

1 3

- Housing
Aluminum
Anodized finish, natural color **ALN**
Anodized finish, black **ALS**
- Spirit level element
Glass plastic body
Filling
Colorless transparent **K**
- Casting compound
Mineral-based
- RoHS compliant

Information

GN 2280 bull's eye spirit levels are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The mounting threads offset by 120° allow the spirit levels to be aligned in relation to the mounting surface. An alignment ball at the bottom surface of the adjustment plate serves as a tilting point.

Specific tightening torques of the bolts are allowed to be achieved, so that the bubble is centrally located inside the marking ring once the horizontal alignment is reached.

see also...

- *General Information on Bull's Eye Spirit Levels and Screw-On Spirit Levels*

On request

- Green transparent filling
- Other sensitivities
- Housing in brass or stainless steel

How to order

GN 2280-ALS-20-K-30

1	Color
2	Outside diameter d_1
3	Filling
4	Sensitivity