

**Metric table**

2 3

Dimensions in: millimeters - inches

d <sub>1</sub>	h <sub>9</sub>	I <sub>1</sub>						d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	l <sub>7</sub>	s <sub>1</sub>	s <sub>2</sub>	Suitable key ring Ø for type E		Suitable spring cotter pins for identification no. 2	
8	.31	16	20	24	28	30	32	2.5	12	2.5	4.3	5.5	7	13.5	18	10	2	3	4	14	-	-	GN 1024-NI-2-D
8	.31	35	40	45	50	55	60	2.5	12	2.5	4.3	5.5	7	13.5	18	10	2	3	4	14	-	-	GN 1024-NI-2-D
10	.39	20	24	30	35	40	45	2.5	15	2.5	4.3	6	7	15	21	11	4	3	4	14	-	-	GN 1024-NI-2-E / ...-D
10	.39	50	55	60	65	70	80	2.5	15	2.5	4.3	6	7	15	21	11	4	3	4	14	-	-	GN 1024-NI-2-E / ...-D
12	.47	20	24	30	35	40	45	2.5	17	3	5.3	7	9	18.5	23	12	4	4	4.5	14	18	-	GN 1024-NI-2-E / ...-D
12	.47	50	55	60	65	70	80	2.5	17	3	5.3	7	9	18.5	23	12	4	4	4.5	14	18	-	GN 1024-NI-2-E / ...-D
16	.63	32	35	40	45	50	55	3.5	22	3	5.3	8	9	21	28	15	6	4	4.5	14	18	-	GN 1024-NI-3-E / ...-D
16	.63	60	65	70	80	90	100	3.5	22	3	5.3	8	9	21	28	15	6	4	4.5	14	18	-	GN 1024-NI-3-E / ...-D
20	.79	40	45	50	55	60	65	4.5	26	3.5	6.4	10.5	9	24	31	17	6	4	5	14	18	24	GN 1024-NI-4-E / ...-D
20	.79	70	80	90	100	-	-	4.5	26	3.5	6.4	10.5	9	24	31	17	6	4	5	14	18	24	GN 1024-NI-4-E / ...-D

**Application example**

