



SS Stainless Steel

**3 Type**

- A With threaded stud
- B With tapped spindle

**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> ±0.04	l <sub>3</sub> ±0.04	A/F	t min.
.98 25	1/4 x 20	.39 10	.43 11	1.48 37.5	.59 15	.31 8	.39 10
1.26 32	5/16 x 18	.51 13	.51 13	1.89 48	.75 19	.39 10	.47 12
1.57 40	3/8 x 16	.63 16	.55 14	2.40 61	.94 24	.55 14	.63 16
1.97 50	1/2 x 13	.79 20	.83 21	3.07 78	1.22 31	.67 17	.63 16

**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> ±1	l <sub>3</sub> ±1	A/F	t min.
25 .98	M 6	10 .39	11 .43	37.5 1.48	15 .59	8 .31	10 .39
32 1.26	M 8	13 .51	13 .51	48 1.89	19 .75	10 .39	12 .47
40 1.57	M 10	16 .63	14 .55	61 2.40	24 .94	14 .55	16 .63
50 1.97	M 12	20 .79	21 .83	78 3.07	31 1.22	17 .67	16 .63

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, glossy finish
- **GN 319.2**  
Spindle  
Steel, zinc plated, blue passivated finish
- **GN 319.5**  
Spindle  
Stainless steel  
European Standard No. 1.4305 (AISI 303),  
matte shot-blasted finish
- RoHS compliant

**Information**

GN 319.2 and GN 319.5 both the threaded stud and tapped spindle type revolving ball knobs can be utilized instead of revolving handles e.g., with handwheels or crank handles.

Revolving ball knobs have the same thread assembly dimensions as the DIN 39, DIN 98, and GN 598 fixed and revolving handles.

see also...

- *Softline Revolving Mushroom Shaped Knobs EN 597.1*

How to order (Inch, steel) <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN 319.2-40-3/8X16-B</b>	1 Ball diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Type

How to order (Metric, stainless steel) <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN 319.5-32-M8-B</b>	1 Ball diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Type