



- 2 Type**
- A** Mounting from the back (tapped blind hole)
  - B** Mounting from the operator's side

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> $l_1 \pm 0.25$	<b>a</b>	<b>b</b>	<b>d<sub>1</sub></b> Type A	<b>d<sub>2</sub></b> Type B	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>l<sub>2</sub></b>	<b>t</b>
120 4.72	14 .55	22 .87	M 6	6.5 .26	44 1.73	5 .20	141.2 5.56	13 .51
140 5.51	18 .71	28 1.10	M 8	8.5 .33	55 2.17	6 .24	166.5 6.56	17 .67

**Specification**

- Aluminum die-cast
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Blank, ground finish



- RoHS compliant

**On request**

- Other finishes

**Information**

GN 328 cabinet “U” handles have excellent stability and ergonomic design. The finger recesses on the underside of the handle provide an especially comfortable grip.

In combination with the larger GN 428 cabinet “U” handle, they meet the requirements of modern industrial design.

see also...

- Cabinet “U” Handles GN 565
- Cabinet “U” Handles GN 428

How to order <b>GN 328-120-A-SW</b>	<b>1</b>	<b>Length <math>l_1</math></b>
	<b>2</b>	<b>Type</b>
	<b>3</b>	<b>Finish</b>