



3 Type

- A Mounting from the back (tapped blind hole)

Metric table

Dimensions in: millimeters - inches

d ₁	Length l ±0.25					d ₂ Thread	b ₁	b ₂	h ₁	h ₂	t min.
28 <i>1.10</i>	242 <i>9.53</i>	292 <i>11.50</i>	392 <i>15.43</i>	492 <i>19.37</i>	592 <i>23.31</i>	M 8	25 <i>0.98</i>	14 <i>0.55</i>	50 <i>1.97</i>	66 <i>2.60</i>	15 <i>0.59</i>

Specification

- Tube
Aluminum (wall thickness 1.5 mm)
- Handle legs
Zinc die-cast, powder coated
- Covers
Plastic
- Tube / handle legs **SW**
Powder coated
Black, RAL 9005, textured finish
Covers
Black, matte finish
- Tube **ELS**
Anodized finish, natural color
Handle legs
Black, RAL 9005, textured finish
Covers
Black, matte finish
- Tube **ELG**
Anodized finish, natural color
Handle legs
Silver, RAL 9006, textured finish
Covers
Light gray, matte finish
- [Load Rating Information](#) → page QVX
- [RoHS compliant](#)

Information

The spacing of the attachment holes of GN 333.3 tubular handles is adjustable. Additional handle legs can be added for very long tubular handles.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.9.

GN 333.3 tubular handles are supplied unassembled.

see also...

- [Handle Tubes GN 930](#) → page QVX

Accessory

- Straight handle legs GN 333.9 → page QVX

On request

- Special tube lengths other than listed

<p>How to order</p> <p>GN 333.3-28-592-A-ELG</p>	1	Handle diameter d ₁
	2	Length l
	3	Type
	4	Finish