



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	Length l ±0.5						b <sub>1</sub>	b <sub>2</sub>	d <sub>2</sub> Thread	h <sub>1</sub>	h <sub>2</sub>	t min.
	200	250	300	400	500	600						
28	200	250	300	400	500	600	25	14	M 8	50	66	15
1.10	7.87	9.84	11.81	15.75	19.69	23.62	0.98	0.55		1.97	2.60	0.59

**Specification**

- Tube Ø 28 x 2 mm  
Stainless steel AISI 304  
Ground, matte shiny finish
- Handle legs  
Stainless steel precision casting AISI CF-8  
Matte shot-blasted finish
- [Load Rating Information](#) → page 2068
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

**Information**

The tube of GN 333.7 tubular handles is pressed together with the handle legs.

see also...

- [Cabinet "U" Handles GN 426.5 \(Stainless Steel\)](#) → page 147
- [Cabinet "U" Handles GN 565.5 \(Stainless Steel, Mounting from the Back or from the Operator's Side\)](#) → page 100
- [Tubular Grip Handles GN 666.5 \(Stainless Steel, Mounting from the Back\)](#) → page 186
- [Tubular Handles GN 333.1 \(Aluminium, Zinc Die-Cast\)](#) → page 164

How to order	1	Handle diameter d <sub>1</sub>
	2	Length l

**GN 333.7-28-400**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4