



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d	l <sub>1</sub>	l <sub>2</sub> ≈	h ≈
10 0.39	64 ±0.25 2.52 ±0.01	75 2.95	35 1.38
10 0.39	96 ±0.25 3.78 ±0.01	111 4.37	35 1.38
10 0.39	128 ±0.25 5.04 ±0.01	146 5.75	35 1.38
10 0.39	160 ±0.25 6.30 ±0.01	181 7.13	35 1.38
10 0.39	192 ±0.35 7.56 ±0.014	219 8.62	35 1.38

**Specification**

- GN 424.1**  
Steel  
Powder coated  
Black, RAL 9005, textured finish ● **SW**  
Silver, RAL 9006, textured finish ● **SR**
- GN 424.5**  
Stainless steel AISI 303  
Matte brushed finish
- Load Rating Information → page 2068
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**On request**

- Various metric size fasteners and kit packaging

**Information**

GN 424.1 and GN 424.5 arched pull handles are preferably used for such applications where easy sliding of folding doors or cabinet drawers can be operated with a single finger. Their shape blends well with modern design.

see also...

- Arch Pull Handles GN 565.4  
(Aluminum, Mounting from the Back or from the Operator's Side) → page 155

How to order (Steel) <b>GN 424.1-10-160-SW</b>	1	Handle diameter d
	2	Length l <sub>1</sub>
	3	Finish
How to order (Stainless steel) <b>GN 424.5-10-128</b>	1	Handle diameter d
	2	Length l <sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4