



SS Stainless Steel

Metric table

1

Dimensions in: millimeters - inches

Length l ±0.25	h ₁	h ₂
100 3.94	34 1.34	43 1.69
120 4.72	34 1.34	43 1.69
180 7.09	34 1.34	43 1.69

Specification

2

- Steel
Chrome-plated finish **CR**
- Stainless steel **NI**
European Standard No. 1.4305 (AISI 303),
matte shot-blasted finish
- Hexagon nuts ISO 8675-M10x1
Stainless steel
European Standard No. 1.4301 (AISI 304)
- Location disks DIN 125
Stainless steel
European Standard No. 1.4301 (AISI 304)
- RoHS compliant

Information

GN 425.2 folding handles are used in such applications where minimal protrusion is required. In both positions the handle is retained by a spring loaded detent pin.

see also...

- *Folding Cabinet „U“ Handles GN 425.8 (with Locking or Spring-Loaded Return)*
- *Folding Handles EN 825.1 (Plastic, with Spring-Loaded Return)*

<p>How to order</p> <p>GN 425.2-180-NI</p>	1	Length l
	2	Material