



SS Stainless Steel

3 Type

- A Thread for mounting from the back
- B Through hole for mounting from the operator's side
- C Mounting from the operator's side by welding

4 Identification no.

- 1 Handle 90° foldaway
- 2 Handle 90° foldaway, with retaining spring
- 3 Handle 180° foldaway
- 4 Handle 180° foldaway, with retaining spring

Metric table

1

Dimensions in: millimeters - inches

Length l	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub>	h <sub>4</sub>	m	t <sub>1</sub>	t <sub>2</sub>
120 4.72	124 4.88	20 .79	106 4.17	M 6	6.4 .25	16 .63	53 2.09	49 1.93	59 2.32	60 2.36	10 .39	9.6 .38

Specification

2

5

- Attachment part  
Stainless steel precision casting **NI**  
European Standard No. 1.4308 (AISI CF-8)  
- Matte, shot-blasted finish **GS**  
- Powder coated (only Type A and B)  
Black, RAL 9005, textured finish **SW**
- Folding handle  
Stainless steel  
European Standard No. 1.4301 (AISI 304),  
matte shot-blasted finish
- Retaining springs  
Spring steel  
European Standard No. 1.4310 (AISI 301)
- RoHS compliant

Information

GN 425.9 stainless steel folding handles are used where the handle must only protrude a short distance in the resting position.

Folding handles identification numbers 1 and 2 are suitable for side "access", as these have a 90° limit stop. If used from above, identification numbers 3 and 4 with a handle that can fold freely through 180° are a better version.

The retaining springs of identification numbers 2 and 4 keep the handle in any position. This keeps the handle in a position that can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

- Folding Handles with Recessed Tray GN 425.8

How to order

1 2 3 4 5  
GN 425.9-120-NI-A-1-SW

1	Length l
2	Material
3	Type
4	Identification no.
5	Finish