



**4 Type**

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

**Metric table**

Dimensions in: millimeters - inches

b	l <sub>1</sub>	a	d Thread	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	t
28 1.10	250 9.84	18 .71	M 8	63 2.48	11.8 .46	290 11.42	30 1.18	10 .39	10 .39
28 1.10	300 11.81	18 .71	M 8	63 2.48	11.8 .46	340 13.39	30 1.18	10 .39	10 .39
28 1.10	400 15.75	18 .71	M 8	63 2.48	11.8 .46	440 17.32	30 1.18	10 .39	10 .39
36 1.42	300 11.81	26 1.02	M 10	71 2.80	16.6 .65	355 13.98	40 1.57	13 .51	14 .55
36 1.42	400 15.75	26 1.02	M 10	71 2.80	16.6 .65	455 17.91	40 1.57	13 .51	14 .55
36 1.42	500 19.69	26 1.02	M 10	71 2.80	16.6 .65	555 21.85	40 1.57	13 .51	14 .55
36 1.42	600 23.62	26 1.02	M 10	71 2.80	16.6 .65	655 25.79	40 1.57	13 .51	14 .55
36 1.42	800 31.50	26 1.02	M 10	71 2.80	16.6 .65	855 33.66	40 1.57	13 .51	14 .55

**Specification**

- Aluminum **AL**
- Powder coated
- Black, RAL 9005, textured finish **● SW**
- Anodized finish, natural color **● EL**
- Type B
- Socket button head screws ISO 7380
- Hexagon nuts ISO 4032
- Washers DIN 125
- Stainless steel
- European Standard No. 1.4301 (AISI 304)
- RoHS compliant

**Information**

GN 428 cabinet “U” handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design. The manufacturing process allows the production of special designs in relatively small quantities.

For type B, socket button head screws, hexagon nuts and washers are included.

Especially in combination with the smaller GN 328 cabinet “U” handles, they meet the requirements of modern industrial design.

see also...

- Cabinet “U” Handles GN 426 (Aluminum)

**On request**

- Other finishes or special designs
- Various metric size fasteners along with kit packaging

**How to order**

1 2 3 4 5  
**GN 428-AL-28-300-A-SW**

1	<b>Material</b>
2	<b>Handle diameter b</b>
3	<b>Length l<sub>1</sub></b>
4	<b>Type</b>
5	<b>Finish</b>