



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Thread	² d ₂ H7	d ₃ -0.3	d ₄	Length l	s -0.15	t min.
M 6	8 .31	18 .71	8.5 .33	19 .75	9 .35	9 .35
M 8	10 .39	20 .79	11 .43	24 .94	12 .47	11 .43
M 10	12 .47	25 .98	13.5 .53	28 1.10	14 .55	14 .55
M 12	16 .63	32 1.26	16 .63	34 1.34	17 .67	16 .63

Specification

- Steel
 - Property class 5
 - Blackened finish
- RoHS compliant

On request

- For certain minimum quantities, inch size threads and bores

Information

In combination with set screws or double ended threaded studs (i.e. DIN 913 or DIN 6379), GN 444.2 eye nuts can be used as swing bolts in varying lengths.

In addition, used with a DIN 912 socket cap screw, a swiveling clamping screw can be produced.

Dimensions d₂, d₃ and s are identical to DIN 444.

For eye nut thread sizes M6, M8 M10 and M12, GN 732.1 cylinder head shoulder bolts can be used as bearing pins.

see also...

- Set Screws GN 913.3
- Double Ended Threaded Studs DIN 6379
- Cylinder Head Shoulder Bolts GN 732.1
- Joint Pieces GN 752

How to order ¹ ² GN 444.2-M10-12	1 Thread d ₁
	2 Eye diameter d ₂