



ELESA original design VCRT.

**3 Type**

- A Without cap
- B With cap

**Metric table**

Dimensions in: millimeters - inches													
<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Thread		<b>2</b> s H9 Square				d <sub>3</sub>	d <sub>4</sub> -0.5	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	
40 1.57	M 8	-	V 6	-	-	-	17 .67	13 .51	17 .67	1 .04	10 .39	14.5 .57	
50 1.97	M 8	-	V 6	V 7	-	-	19 .75	16 .63	20 .79	1.2 .05	10 .39	17.5 .69	
63 2.48	M 10	M 12	V 6	V 7	V 8	-	22.5 .89	20 .79	21.5 .85	1.3 .05	10 .39	19 .75	
74 2.91	M 10	M 12	V 7	V 8	V 9	V 10	26.5 1.04	20 .79	24.5 .96	2 .08	14.5 .57	21 .83	
95 3.74	M 16	-	V 8	V 10	-	-	32 1.26	18 .71	29.5 1.16	4.5 .18	14.5 .57	26.5 1.04	

**Specification**

- Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 266 °F (130 °C)
  - Black, matte finish
- Tapped insert / square bushing  
Brass
- RoHS compliant

**Information**

EN 5331 five lobed knobs are resistant to solvents, oils, grease and other chemical agents.

**On request**

- Cover caps in other colors  
(standard color: black)

How to order <b>EN5331-63-M10-A</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub> (Square s)
	<b>3</b>	Type