



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread		d ₃	h ₁	h ₂	t min.
	MS Insert	NI Insert				
63 2.48	M 8	M 10	23 0.91	30.5 1.20	16 0.63	13 0.51
80 3.15	M 10	M 12	30.5 1.20	37 1.46	20 0.79	17 0.67
100 3.94	M 12	M 14	35 1.38	43 1.69	23 0.91	20 0.79

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped insert
- Brass **MS**
- Stainless steel AISI 303 **NI**
- Color of the cover cap (matte finish):
 - DSW Black, RAL 9005
 - DOR Orange, RAL 2004
 - DGR Gray, RAL 7035
 - DGB Yellow, RAL 1021
 - DBL Blue, RAL 5024
 - DRT Red, RAL 3000
 - DGN Green, RAL 6017
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Information

The ergonomic shape of the EN 533 three-lobed knobs supports effective gripping, resulting in a high torque.

see also...

- Three-Lobed Knobs GN 5345 → page QVX
- Three-Lobed Knobs EN 5330 (Plastic) → page QVX

How to order	
1	Handle diameter d ₁
2	Thread d ₂
3	Insert material
4	Color of the cover cap

EN 533-63-M8-MS-DSW