



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	³ Length l	d ₃	h ₁	h ₂
63 2.48	M 8	25 0.98	23 0.91	30.5 1.20	16 0.63
80 3.15	M 10	30 1.18	30.5 1.20	37 1.46	20 0.79
100 3.94	M 12	40 1.57	35 1.38	43 1.69	23 0.91

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Threaded stud
Steel zinc plated, blue passivated finish
- Color of the cover cap (matte finish):
 - DSW
 - DOR
 - DGR
 - DGB
 - DBL
 - DRT
 - DGN
- Plastic Characteristics → page QVX
- RoHS compliant

Information

The ergonomic shape of the EN 533 three-lobed knob with threaded stud supports effective gripping, resulting in a high torque.

see also...

- Three-Lobed Knobs GN 5345 → page QVX
- Three-Lobed Knobs EN 5330 (Plastic) → page QVX

How to order ¹ ² ³ ⁴ EN 533-100-M12-40-DSW	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l
	4 Color of the cover cap