



**3 Type**

- A Without eyelet
- B With eyelet

**Universal table**

**2**

Dimensions in: millimeters - inches

d <sub>1</sub>	b	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	Nominal magnetic force
17 0.67	6 0.24	12 0.47	4 0.16	22.5 0.89	6 0.24	35 N 7.87 lbf

**Specification**

**1**

**4**

- Magnet material  
NdFeB **ND**  
Neodymium, iron, boron  
Temperature resistant up to 176 °F (80 °C)
- Housing  
Plastic
  - White, RAL 9003  **WS**
  - Gray, RAL 7040  **GR**
  - Black, RAL 9004  **SW**
  - Red, RAL 3031  **RT**
- Countersunk screw  
Stainless steel
- RoHS compliant

**Information**

Retaining magnets GN 53.3 work in combination with the ergonomic plastic handle as a system for holding documents, templates, drawings etc. that are used in technical environments.

The neodymium magnet keeps the required contact diameter small while also supplying a high retaining force.

Type B with eyelet also offers the ability to protect the magnet from being lost with a retaining cable.

see also...

- *More Information on Retaining Magnets* → page QVX
- *Magnets GN 53.4 (Disk-Shaped, with Handle)* → page QVX
- *Retaining Magnets GN 53.1 (Disk-Shaped)* → page QVX
- *Retaining Magnets GN 53.2 (Rectangular-Shaped)* → page QVX
- *Retaining Magnets GN 51.7 (with Ball Knob / with Key Ring)* → page QVX

**Accessory**

- Holding disks GN 70 → page QVX
- Self-adhesive disks GN 70.1 → page QVX
- Retaining cables GN 111.2 → page QVX
- Spiral retaining cables GN 111.4 → page QVX

**On request**

- Other colors

How to order	
<b>1</b>	Magnet material
<b>2</b>	Diameter d <sub>1</sub>
<b>3</b>	Type
<b>4</b>	Color

**GN 53.3-ND-17-A-GR**