



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
40	M 6	18	18.8	30.5	15	12
40	M 8	18	18.8	30.5	15	15
50	M 8	21	21.8	34	17	15
50	M 10	21	21.8	34	17	18

### Specification

- **Stainless Steel**
  - AISI 316 L (A4)
  - Matte shot blast finish
  - Polished (Ra < 0.8 µm)
- **Sealing Ring**
  - Hydrogenated acrylonitrile butadiene rubber (H-NBR)
  - Blue
  - Temperature resistant -25 °C to +150 °C
  - Hardness 85±5 Shore A
  - FDA compliant



### Information

GN 5435 star knobs are intended for use in hygienic design applications. The sealed mounting surface enables fastening without dead spaces. The high quality finish and the large corner radii prevent adherence of dirt and facilitates cleaning.

GN 5435 Star Knobs with inch size threads are available upon request.

see also...

- *Sealing rings GN 7600* → Page 16

**MT**  
**PL**

- **RoHS compliant**

#### How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**GN 5435-40-M8-PL**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Finish