



ELESA Original design T.470

Metric table



Dimensions in: millimeters - *inches*

d ₁ Thread		d ₂	Length l	t
G 1	-	42 1.65	16 0.63	11 0.43
G 2	M 60 x 2	70 2.76	26 1.02	18 0.71

Specification

- Cap
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal
NBR rubber (Perbunan®)
- RoHS compliant

How to order

EN548.2-G1

1 Thread d₁