



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side (only for $b_1 = 26$ mm)

Metric table

Dimensions in: millimeters - inches

b₁	Length $l \pm 0.25$	a	b₂	b₃	b₄	b₅ +1	d₁ Type A	d₂ Type B	h₁	h₂	r	t min.
20 0.79	112 4.41	13 0.51	24 0.94	32 1.26	50 1.97	13.5 0.53	M 6	-	32 1.26	48 1.89	13 0.51	10 0.39
20 0.79	128 5.04	13 0.51	24 0.94	32 1.26	50 1.97	13.5 0.53	M 6	-	32 1.26	48 1.89	13 0.51	10 0.39
26 1.02	128 5.04	17 0.67	32 1.26	34 1.34	57 2.24	18 0.71	M 8	M 6	34 1.34	54 2.13	17 0.67	12 0.47
26 1.02	160 6.30	17 0.67	32 1.26	34 1.34	57 2.24	18 0.71	M 8	M 6	34 1.34	54 2.13	17 0.67	12 0.47

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
 - Anodized finish, natural color **● EL**
 - Plain, tumbled finish **● BL**
- Type B
 - Socket button head screws ISO 7380-M6-25
 - Hex nuts ISO 4032-M6
 - Washers DIN 125
- Steel, zinc plated, blue passivated finish
- [Load Rating Information](#) → page 2068
- [RoHS compliant](#)

Information

GN 565.2 angled cabinet “U” handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design. The 35° angled contact surface allows improved access even in tight spaces such as corners.

The manufacturing process allows the production of special lengths in relatively small quantities.

For type B, socket button head screws, hex and washers are included.

see also...

- [Product Family Standard Parts for Profile Systems](#) → page 18
- [Cabinet “U” Handles GN 425.1 \(Offset\)](#) → page 144 / 145
- [Cabinet “U” Handles GN 426.1 \(Offset Round Aluminum\)](#) → page 150
- [Off-Set Open “U” Handles EN 630.1 \(Technopolymer Plastic\)](#) → page 108
- [T-Nut Assemblies GN 965 \(for 30 / 40 mm T-Slot Profile Systems\)](#) → page 2048
- [T-Nut Assemblies GN 968 \(for 30 / 40 / 45 mm T-Slot Profile Systems\)](#) → page 2058

On request

- Special lengths

How to order	1	Handle width b_1
	2	Length l
	3	Type
	4	Finish

1 2 3 4
GN 565.2-26-128-B-SW