



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table

Dimensions in: millimeters - inches

1 b	2 $l_1 \pm 0.25$	l_2 Type A	$l_3 \approx$ Type B	a	d_1 Type A	d_2 Type B	h_1	h_2 Type B	r	t min.
20 .79	120 4.72	142 5.59	137 5.39	13 .51	M 5	5.3 .21	41 1.61	5 .20	13 .51	10 .39
20 .79	160 6.30	182 7.17	177 6.97	13 .51	M 5	5.3 .21	45 1.77	5 .20	13 .51	10 .39

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
 - Anodized finish, natural color
 - Blank, tumbled finish

- **SW**
- **SR**
- **EL**
- **BL**

- RoHS compliant

Information

The standard usage of GN 565.3 cabinet "U" handles is made for light duty applications such as metal covers or machine guards.

Center distance is the same for the top and for the bottom-mount versions, which gives both handles the ability to be mounted to each other through the mounting surface they are placed on.

The manufacturing process allows the production of special lengths in relatively small quantities.

On request

- Special lengths
- Various metric size fasteners and kit packaging

How to order	
1 Handle width b	
2 Length l_1	
3 Type	
4 Finish	

GN 565.3-20-120-B-SW