



SS Stainless Steel

3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table

Dimensions in: millimeters - inches

1 b		2 $l_1 \pm 0.25$	$l_2 \approx$	a	d_1	d_2	$h_1 \approx$	h_2	t_1 min.	t_2
GN 565.4	GN 565.9				Type A	Type B				
20 0.79	20 0.79	160 6.30	185 7.28	13 0.51	M 6	5.3 0.21	50 1.97	5 0.20	8 0.31	5 0.20
20 0.79	20 0.79	192 7.56	221 8.70	13 0.51	M 6	5.3 0.21	50 1.97	5 0.20	8 0.31	5 0.20
26 1.02	-	160 6.30	190 7.48	17 0.67	M 8	6.4 0.25	57 2.24	6 0.24	11 0.43	6 0.24
26 1.02	-	192 7.56	227 8.94	17 0.67	M 8	6.4 0.25	57 2.24	6 0.24	11 0.43	6 0.24

Specification

- **GN 565.4**
Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Red, RAL 3000, textured finish
 - Silver, RAL 9006, textured finish
 - Anodized finish, natural color
 - Blank, tumbled finish
- **GN 565.9**
Stainless steel
European Standard No. 1.4301 (AISI 304)
Matte shot-blasted finish **MT**
- **RoHS compliant**

- **SW**
- **RS**
- **SR**
- **EL**
- **BL**

Information

GN 565.4 and GN 565.9 arched pull handles are preferably used for such applications where easy sliding of folding doors or cabinet drawers can be operated with a single finger. Their shape blends well with modern design.

The manufacturing process allows the production of special lengths in relatively small quantities.

see also...

- *Arched Pull Handles GN 665 (Aluminum, Ellipse Shaped Profile)*
- *Arched Pull Handles GN 424.1 / GN 424.5 (Steel / Stainless Steel, Ø 10 mm)*

On request

- Special lengths
- Various metric size fasteners and kit packaging

How to order (Aluminum)	1 Handle width b
1 2 3 4	2 Length l₁
GN 565.4-20-160-B-RS	3 Type
	4 Finish

How to order (Stainless steel)	1 Handle width b
1 2 3 4	2 Length l₁
GN 565.9-20-192-A-MT	3 Type
	4 Finish