



SS Stainless Steel

**3 Type**

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

**Metric table**

Dimensions in: millimeters - inches

b		l <sub>1</sub> ±0.25	l <sub>2</sub> ≈	a	d <sub>1</sub> Type A	d <sub>2</sub> Type B	h <sub>1</sub> ≈	h <sub>2</sub>	t <sub>1</sub> min.	t <sub>2</sub>
GN 565.4	GN 565.9									
20	20	160	185	13	M 6	5.3	50	5	8	5
0.79	0.79	6.30	7.28	0.51		0.21	1.97	0.20	0.31	0.20
20	20	192	221	13	M 6	5.3	50	5	8	5
0.79	0.79	7.56	8.70	0.51		0.21	1.97	0.20	0.31	0.20
26	-	160	190	17	M 8	6.4	57	6	11	6
1.02		6.30	7.48	0.67		0.25	2.24	0.24	0.43	0.24
26	-	192	227	17	M 8	6.4	57	6	11	6
1.02		7.56	8.94	0.67		0.25	2.24	0.24	0.43	0.24

**Specification**

**GN 565.4**

- Aluminum
- Powder coated
- Black, RAL 9005, textured finish
- Red, RAL 3000, textured finish
- Silver, RAL 9006, textured finish
- Anodized finish, natural color
- Plain, tumbled finish

- SW
- RS
- SR
- EL
- BL

**GN 565.9**

- Stainless steel AISI 304
- Matte shot-blasted finish

MT

- Load Rating Information → page 2068
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**On request**

- Special lengths
- Various metric size fasteners and kit packaging

**Information**

GN 565.4 and GN 565.9 arched pull handles are preferably used for such applications where easy sliding of folding doors or cabinet drawers can be operated with a single finger. Their shape blends well with modern design.

The manufacturing process allows the production of special lengths in relatively small quantities.

see also...

- Arched Pull Handles GN 665 (Aluminum, Ellipse Shaped Profile) → page 156
- Arched Pull Handles GN 424.1 / GN 424.5 (Steel / Stainless Steel, Ø 10 mm) → page 157

How to order (Aluminum)	1 Handle width b
1 2 3 4	2 Length l <sub>1</sub>
<b>GN 565.4-20-160-B-RS</b>	3 Type
	4 Finish
How to order (Stainless steel)	1 Handle width b
1 2 3 4	2 Length l <sub>1</sub>
<b>GN 565.9-20-192-A-MT</b>	3 Type
	4 Finish