



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁		d ₂	d ₃	l ₁ ≈	l ₂	l ₃	l ₄ ≈	l ₅
GN 598.3	GN 598.5	Thread						
18 0.71	-	M 5	16 0.63	57 2.24	15 0.59	5 0.20	52 2.05	9.5 0.37
21 0.83	-	M 5	16 0.63	67 2.64	15 0.59	5 0.20	62 2.44	9.5 0.37
22 0.87	-	M 5	16 0.63	73 2.87	15 0.59	5 0.20	68 2.68	9.5 0.37
23 0.91	23 0.91	M 6	20 0.79	87 3.43	19.5 0.77	6 0.24	80 3.15	10.5 0.41
26 1.02	26 1.02	M 6	20 0.79	102 4.02	19.5 0.77	6 0.24	95 3.74	10.5 0.41
28 1.10	28 1.10	M 8	26 1.02	118 4.65	26 1.02	10 0.39	106 4.17	16 0.63

Specification

- Handle
Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Revolving
- Handle holds in both positions
- **GN 598.3**
Retractable mechanism
Steel, blackened finish
- **GN 598.5**
Retractable mechanism
- Stem, retaining pin
Stainless steel AISI 303
- Hub
Sintered steel AISI 316LHC
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

On request

- Technopolymer plastic hand piece

Information

GN 598.3 and GN 598.5 retractable handles are suitable when the handle must be withdrawn during automatic operation.

The handle is pulled out of its tapered seat in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions. A positive lock is achieved in the operating position by way of a tapered seat located in the hub of the mechanism.

see also...

- *Safety Retractable Handles GN 798.7 (Automatic Fold-Down Type, Steel)* → page 49
- *Safety Retractable Handles GN 798.8 (Automatic Fold-Down Type, Stainless Steel)* → page 49

How to order (Steel)	1	Material
GN598.3-KU-26	2	Handle diameter d ₁

How to order (Stainless steel)	1	Material
GN598.5-KU-23	2	Handle diameter d ₁