



ELESA original design M.843



Dimensions in: inches - millimeters

Inch table

Length l	d Thread	a	b	h	t min.
3.39 ±0.02* 86 ±0.5	1/4 x 20	.67 17	1.02 26	1.83 46.5	.47 12
4.61 ±0.02* 117 ±0.5	5/16 x 18	.79 20	1.18 30	2.09 53	.51 13
7.05 ±0.04* 179 ±1.0	5/16 x 18	.79 20	1.18 30	2.44 62	.51 13

Metric table

Length l	d Thread	a	b	h	t min.
86 ±0.5 3.39 ±0.02	M 6	17 .67	26 1.02	46.5 1.83	12 .47
117 ±0.5 4.61 ±0.02	M 8	20 .79	30 1.18	53 2.09	13 .51
179 ±1.0 7.05 ±0.04	M 8	20 .79	30 1.18	62 2.44	13 .51
300 ±1.0 11.81 ±0.04	M 8	22 .87	32 1.26	64 2.52	13 .51

* Inch sizes are only available in color SW

Specification

- Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to 248 °F (120 °C)
- Colors (glossy finish):
 - Black, RAL 9005 ● SW
 - Orange, RAL 2004 ● OR
 - Red, RAL 3000 ● RT
 - White, RAL 9002, Cleanline ● CL
 - Yellow, RAL 1021 ● GB
 - Gray, RAL 7035 ● GR
 - Blue, RAL 5024 ● BL
- Tapped inserts
 - Standard: brass, molded-in
 - Cleanline version (CL): stainless steel
- RoHS compliant

Information

EN 625 cabinet "U" handles have an ergonomic design and aesthetically appealing glossy finish.

see also...

- Product Range Cleanline
- Cabinet "U" Handles GN 565 (Aluminum)
- Cabinet "U" Handles EN 725 (Technopolymer Plastic)

On request

- Inch sizes in additional colors
- Various inch and metric size fasteners and kit packaging

How to order (Inch)	1 Length l
EN 625-86-1/4X20-SW	2 Thread d
	3 Color

How to order (Metric)	1 Length l
EN 625-117-M8-RT	2 Thread d
	3 Color