



**Inch table**

Length <b>l</b>	<b>d</b> Thread	<b>a</b>	<b>b</b>	<b>h</b>	<b>t</b> min.
3.39 ±0.02* 86 ±0.5	1/4 x 20	0.67 17	1.02 26	1.83 46.5	0.47 12
4.61 ±0.02* 117 ±0.5	5/16 x 18	0.79 20	1.18 30	2.09 53	0.51 13
7.05 ±0.04* 179 ±1.0	5/16 x 18	0.79 20	1.18 30	2.44 62	0.51 13

Dimensions in: inches - millimeters

**Metric table**

Length <b>l</b>	<b>d</b> Thread	<b>a</b>	<b>b</b>	<b>h</b>	<b>t</b> min.
86 ±0.5 3.39 ±0.02	M 6	17 0.67	26 1.02	46.5 1.83	12 0.47
117 ±0.5 4.61 ±0.02	M 8	20 0.79	30 1.18	53 2.09	13 0.51
179 ±1.0 7.05 ±0.04	M 8	20 0.79	30 1.18	62 2.44	13 0.51
300 ±1.0 11.81 ±0.04	M 8	22 0.87	32 1.26	64 2.52	13 0.51

Dimensions in: millimeters - inches

\* Inch sizes are only available in color SW

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
Temperature resistant up to 248 °F (120 °C)
- Color (shiny finish)
  - Black, RAL 9005 ● SW
  - Orange, RAL 2004 ● OR
  - Red, RAL 3000 ● RT
  - Yellow, RAL 1021 ● GB
  - Gray, RAL 7035 ● GR
  - Blue, RAL 5024 ● BL
  - Green, RAL 6017 ● GN
  - White, RAL 9002 ● WS
- Tapped inserts
  - Standard: Brass
  - White version (WS): Stainless steel
- Plastic Characteristics
- Strength Values
- RoHS compliant

**Information**

EN 625 cabinet "U" handles have an ergonomic design and aesthetically appealing shiny finish.

see also...

- Cabinet "U" Handles GN 565 (Aluminum)
- Cabinet "U" Handles EN 725 (Technopolymer Plastic)

**On request**

- Various inch and metric size fasteners and kit packaging

How to order (Inch)	1 Length l
<b>EN 625-86-1/4X20-SW</b>	2 Thread d
	3 Color

How to order (Metric)	1 Length l
<b>EN 625-117-M8-RT</b>	2 Thread d
	3 Color