



ELESA original design ESP.



**2 Type**

- A Fixing with hexagon head screw
- B Fixing with countersunk screw

**Metric table**



Dimensions in: millimeters - inches

$l_1$	$l_2 \pm 0.5$	$l_3$	$b_1$	$b_2$	$d$	$h_1$	$h_2$	$h_3$	$h_4$	$t$
114	93.5	74	35	19	6.5	33	7	11	9	5
4.49	3.68	2.91	1.38	.75	.26	1.30	.28	.43	.35	.20

**Specification**



- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 230 °F (110 °C)  
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover (glossy finish):
  - DSG
  - DOR
  - DGR
  - DGB
  - DBL
  - DRT
- Mounting holes  
Counterbored for inch or metric screws
- RoHS compliant

**Information**

When using guards on machines and automation systems, which include double hinged doors, the EN 630 Ergostyle® off-set “U” handles completely enclosed are a safety element for operator fingers while the doors are being used. Use of a colored safety cover makes identification easier.

Resistant to solvents, oils, grease and other chemical agents.

The cover is included but supplied unassembled.

see also...

- Product Range Ergostyle®
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order

**EN 630-114-B-DOR**

1	Length $l_1$
2	Type
3	Color of the cover