



ELESA original design ESP.



2 Type

- A Fixing with hexagon head screw
- B Fixing with countersunk screw

Metric table



Dimensions in: millimeters - inches

l ₁	l ₂ ±0.5	l ₃	b ₁	b ₂	d	h ₁	h ₂	h ₃	h ₄	t
114	93.5	74	35	19	6.5	33	7	11	9	5
4.49	3.68	2.91	1.38	.75	.26	1.30	.28	.43	.35	.20

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover (glossy finish):
 - DSG
 - DOR
 - DGR
 - DGB
 - DBL
 - DRT
- Mounting holes
Counterbored for inch or metric size screws
- RoHS compliant

Information

When using guards on machines and automation systems, which include double hinged doors, the EN 630 Ergostyle® off-set “U” handles completely enclosed are a safety element for operator fingers while the doors are being used. Use of a colored safety cover makes identification easier.

Resistant to solvents, oils, grease and other chemical agents.

The cover is included but supplied unassembled.

see also...

- Product Range Ergostyle®
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order	1 Length l ₁
EN 630-114-B-DOR	2 Type
	3 Color of the cover