



ELESA original design ESP.



**2 Type**

- A Mounting with hexagon head screw
- B Mounting with countersunk screw

**Metric table**



Dimensions in: millimeters - inches

l <sub>1</sub>	l <sub>2</sub> ±0.5	l <sub>3</sub>	b <sub>1</sub>	b <sub>2</sub>	d	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	t
114 4.49	93.5 3.68	74 2.91	35 1.38	19 0.75	6.5 0.26	33 1.30	7 0.28	11 0.43	9 0.35	5 0.20

**Specification**



- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 230 °F (110 °C)  
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover (shiny finish):
  - DSG
  - DOR
  - DGR
  - DGB
  - DBL
  - DRT
  - DGN
- RoHS compliant

**Information**

When using guards on machines and automation systems, which include double hinged doors, the EN 630 Ergostyle® off-set “U” handles completely enclosed are a safety element for operator fingers while the doors are being used. Use of a colored safety cover makes identification easier.

Resistant to solvents, oils, grease and other chemical agents.

The cover is included but supplied unassembled.

see also...

- Product Range Ergostyle®
- Product Range Standard Parts for Profile Systems
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order	
1 2 3	1 Length l <sub>1</sub>
EN 630-114-B-DOR	2 Type
	3 Color of the cover