



ELESA original design EWP.



2 Type

- A** Fixing with hexagon head screw
- B** Fixing with countersunk screw

Metric table



Dimensions in: millimeters - inches

l_1	$l_2 \pm 0.5$	l_3	b_1	b_2	d	h_1	h_2	h_3	h_4	t
114	93.5	74	35	19	6.5	33	7	11	9	5
4.49	3.68	2.91	1.38	.75	.26	1.30	.28	.43	.35	.20

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover caps (glossy finish):

● DSG	Black-gray, RAL 7021
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
- Mounting holes
Counterbored for inch or metric screws
- RoHS compliant

Information

When using guards on machines and automation systems, which include double hinged doors, use of colored covers makes identification of the EN 630.1 Ergostyle® off-set open “U” handles easier.
Resistant to solvents, oils, grease and other chemical agents.
The covers are included but supplied unassembled.

see also...

- Product Range Ergostyle®
- Cabinet “U” Handles GN 565.2
(Aluminum, Angled, Mounting from the Back or from the Operator’s Side)
- Cabinet “U” Handles GN 425.1 (Offset)
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

How to order EN 630.1-114-A-DOR	1 Length l_1
	2 Type
	3 Color of the cover caps