



Metric table

Dimensions in: millimeters - inches

b₁	Length l				Metric bolt size	Inch bolt size	b₂	b₃	h₁	h₂
6.6 .26	60 2.36	-	-	-	M 6	1/4	19 .75	6 .24	12 .47	3 .12
9 .35	80 3.15	-	-	-	M 8	5/16	25 .98	8 .31	15 .59	4 .16
11 .43	100 3.94	-	-	-	M 10	3/8	31 1.22	10 .39	20 .79	5 .20
14 .55	125 4.92	160 6.30	200 7.87	-	M 14	1/2	38 1.50	12 .47	25 .98	6 .24
18 .71	160 6.30	200 7.87	-	-	M 18	5/8	48 1.89	15 .59	30 1.18	8 .31
18 .71	250 9.84	-	-	-	M 18	5/8	48 1.89	15 .59	40 1.57	10 .39
22 .87	200 7.87	-	-	-	M 22	3/4	52 2.05	15 .59	40 1.57	10 .39
22 .87	250 9.84	315 12.40	-	-	M 22	3/4	62 2.44	20 .79	40 1.57	10 .39
22 .87	500 19.69	-	-	-	M 22	3/4	62 2.44	20 .79	50 1.97	10 .39
26 1.02	200 7.87	250 9.84	315 12.40	-	M 24	1	66 2.60	20 .79	40 1.57	10 .39
26 1.02	500 19.69	-	-	-	M 24	1	66 2.60	20 .79	50 1.97	10 .39
33 1.30	250 9.84	315 12.40	400 15.75	600 23.62	M 30	1 1/4	74 2.91	20 .79	50 1.97	12 .47
33 1.30	1000 39.37	-	-	-	M 30	1 1/4	94 3.70	30 1.18	60 2.36	12 .47
40 1.57	400 15.75	600 23.62	-	-	M 36	1 1/2	100 3.94	30 1.18	60 2.36	12 .47
43 1.69	600 23.62	-	-	-	M 42	1 1/2	123 4.84	40 1.57	80 3.15	12 .47

Specification

- Tapered fork clamp
Tempered steel, lacquer painted finish
- RoHS compliant

Information

DIN 6315B tapered fork clamps with open slot have a large offering of clamp size options. They range from 2.36" (60 mm) to 39.37" (1,000 mm) in length with the ability to clamp small to very large parts.

see also...

- Forked Clamps DIN 6315C
- Forked Clamps NO. 6315 GN

<p>How to order</p> <p>DIN 6315B-22-500</p>	1	Width b₁
	2	Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

