



- 3 Type**
- A** Mounting from the back (tapped blind hole)
  - B** Mounting from the operator's side (only for b<sub>1</sub>=20)

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> b <sub>1</sub>	<b>2</b> l <sub>1</sub> ±0.25	a	b <sub>2</sub>	d Thread	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	r	t <sub>1</sub> min.	t <sub>2</sub>
20 .79	130 5.12	10 .39	23 .91	M 5	45 1.77	6.5 .26	2.5 .10	120 4.72	141 5.55	153 6.02	15 .59	10 .39	5 .20
20 .79	170 6.69	10 .39	23 .91	M 5	45 1.77	6.5 .26	2.5 .10	160 6.30	181 7.13	193 7.60	15 .59	10 .39	5 .20
20 .79	190 7.48	10 .39	23 .91	M 5	45 1.77	6.5 .26	2.5 .10	180 7.09	201 7.91	213 8.39	15 .59	10 .39	5 .20
20 .79	210 8.27	10 .39	23 .91	M 5	45 1.77	6.5 .26	2.5 .10	200 7.87	221 8.70	233 9.17	15 .59	10 .39	5 .20
30 1.18	262 10.31	12 .47	-	M 6	50 1.97	-	-	250 9.84	-	-	15 .59	12 .47	-
30 1.18	312 12.28	12 .47	-	M 6	50 1.97	-	-	300 11.81	-	-	15 .59	12 .47	-
30 1.18	362 14.25	12 .47	-	M 6	50 1.97	-	-	350 13.78	-	-	15 .59	12 .47	-
30 1.18	412 16.22	12 .47	-	M 6	50 1.97	-	-	400 15.75	-	-	15 .59	12 .47	-

**Specification**

- Aluminum
  - Powder coated
  - Black, RAL 9005, textured finish
  - Blank, tumbled finish



- Handle base
  - Plastic
  - Technopolymer (Polyamide PA)
  - Black, matte finish

• RoHS compliant

**On request**

- Special lengths
- Various metric size fasteners and kit packaging

**Information**

GN 668 cabinet "U" handles are manufactured from a bent aluminum profile with a smooth surface and rigid design. The shape of the handle has good ergonomic features.

The manufacturing process allows the production of special lengths in relatively small quantities.

see also...

- "Economical" Cabinet "U" Handles GN 728  
(Aluminum, Mounting from the Back or from the Operator's Side)

How to order

**GN 668-20-170-B-SW**

- 1** Handle width b<sub>1</sub>
- 2** Length l<sub>1</sub>
- 3** Type
- 4** Finish