



SS Stainless Steel

3 Type

- A Without knurl
- B With knurl

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread		d ₃	h ₁	h ₂	t min.
21 .83	M 4	M 5	12.5 .49	18 .71	10.5 .41	10
25 .98	M 6	M 8	14.5 .57	22.5 .89	14 .55	12
31 1.22	M 8	-	18.5 .73	27 1.06	17 .67	15
31 1.22	M 10	-	18.5 .73	27 1.06	17 .67	17

Specification

- **GN 676.1**
Steel, blackened finish
- **GN 676.5**
Stainless steel
 - European Standard No. 1.4305 (AISI 303)
 - Matte shot-blasted finish
- RoHS compliant

Information

GN 676.1 and GN 676.5 knobs are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.

The attractively shaped knurled version (Type B) is supplied with a tapped blind hole.

see also...

- Ergostyle® Knurled Knobs EN 676
- Waist Shaped Knobs GN 75
- Waist Shaped Knobs GN 75.5

<p>How to order (Steel)</p> <p>GN 676.1-21-M5-B</p>	<p>1 Handle diameter d₁</p> <p>2 Thread d₂</p> <p>3 Type</p>
<p>How to order (Stainless steel)</p> <p>GN 676.5-31-M10-A</p>	<p>1 Handle diameter d₁</p> <p>2 Thread d₂</p> <p>3 Type</p>

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4