



2 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table



Dimensions in: millimeters - inches

$l_1 \pm 0.25$		b	d_1 Thread	d_2	d_3	h_1	h_2	l_2	l_3	s	t_1 min.	t_2
GN 728	GN 728.5											
120	120	22.5 .89	M 6	6.4 .25	11 .43	42.5 1.67	6.5 .26	147 5.79	108 4.25	8 .31	10 .39	6.5 .26
180	-	27 1.06	M 8	8.4 .33	13.5 .53	47.5 1.87	7.5 .30	214 8.43	165 6.50	10 .39	12 .47	8.5 .33

Specification



GN 728

- Aluminum, pressure die-cast
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Blank, tumbled finish



GN 728.5

- Stainless steel precision casting
- European Standard No. 1.4308 (AISI CF-8)
- Matte shot-blasted finish

RoHS compliant

Information

GN 728 and GN 728.5 "economical" cabinet "U" handles are a low-cost alternative in metal.

The installation can be carried out from the back (type A) as well as from the operator's side (type B). Hole center dimension is identical in both versions, so they can be mounted in pairs opposite each other. Tumbled finish version not recommended to be anodized.

see also...

- Product Range Standard Parts for Profile Systems
- Cabinet "U" Handles EN 528 (Plastic, Mounting from the Operator's Side)
- Cabinet "U" Handles EN 528.1 (Plastic, Mounting from the Back)
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)

On request

- For certain minimum quantities, special colors
- Various metric size fasteners and kit packaging

How to order (Aluminum)	1 Length l_1
GN 728-120-A-SW	2 Type
	3 Finish

How to order (Stainless steel)	1 Length l_1
GN 728.5-120-B	2 Type