



SS Stainless Steel

2 Type

- A** Mounting from the operator's side
- C** Mounting from the back

3 Identification no.

- 1** Without sealing
- 2** With sealing

Metric table

1

Dimensions in: millimeters - inches

l_1	h_1	h_2	l_2	l_3	l_4	l_5	$l_6 + 1$	$l_7 + 1$	m_1	m_2
155	80	42	109	20	3.5	19.2	60	115	128	53
6.10	3.15	1.65	4.29	.79	.14	.76	2.36	4.53	5.04	2.09

Specification

4

- Stainless steel
European Standard No. 1.4301 (AISI 304),
matte shot-blasted finish **GS**
- Housing seal (Identification no. 2)
Black NBR rubber, glued
- Countersunk sealing screws DIN 7991 M5x16
(Type A, Identification no. 2)
- Stainless steel A2
- Polyamide coating on head
- Threaded studs (Type C)
- Stainless steel
European Standard No. 1.4301 (AISI 304)
- Welded
- RoHS compliant

Information

GN 7332 gripping trays can be easily and quickly installed from the front using countersunk screws or from the back with threaded studs. Threaded studs are welded to the gripping tray.

Gripping trays with housing seal (identification no. 2) prevent the penetration of any dirt or liquids into the housing interior. Type A is supplied with four additional countersunk sealing screws, which feature a polyamide coating on the head to create a tight seal.

see also...

- Ergostyle® Gripping Trays EN 733 (Technopolymer Plastic, Screw-In Type)
- Ergostyle® Gripping Trays EN 731 (Technopolymer Plastic, Clip-In Type)

How to order

GN 7332-155-A-1-GS

1 Length l_1

2 Type

3 Identification no.

4 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4