



SS Stainless Steel

- 3 Type**
- O** Without symbol
 - E** With fill symbol
 - A** With drain symbol

- 4 Identification no.**
- 1** Without vent hole

Metric table

Dimensions in: millimeters - inches

1 d_1	2 d_2		d_3	$e \approx$	l_1	l_2	s	t
	Pipe thread	Fine thread	Thread					
19 <i>0.75</i>	G 1/4	M 14 x 1.5	M 5	17.3 <i>0.68</i>	15.5 <i>0.61</i>	8 <i>0.31</i>	15 <i>0.59</i>	8 <i>0.31</i>
22 <i>0.87</i>	G 3/8	M 16 x 1.5	M 5	20.8 <i>0.82</i>	15.5 <i>0.61</i>	8 <i>0.31</i>	18 <i>0.71</i>	8 <i>0.31</i>
26 <i>1.02</i>	G 1/2	M 20 x 1.5	M 5	24.3 <i>0.96</i>	16 <i>0.63</i>	8.5 <i>0.33</i>	21 <i>0.83</i>	8 <i>0.31</i>
32 <i>1.26</i>	G 3/4	M 26 x 1.5	M 5	31.2 <i>1.23</i>	17 <i>0.67</i>	9 <i>0.35</i>	27 <i>1.06</i>	8 <i>0.31</i>
40 <i>1.57</i>	G 1	M 33 x 1.5	M 5	37 <i>1.46</i>	19.5 <i>0.77</i>	11 <i>0.43</i>	32 <i>1.26</i>	8 <i>0.31</i>

Specification

- Body
Stainless steel AISI 316L
Plain, tumbled finish
- Seal
Fluoro-elastomer (FPM / FKM)
- Brown
- Temperature resistant up to 356 °F (180 °C)
- [Plastic Characteristics](#) → page QVX
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

On request

- Other thread sizes
- With dipstick
- With acrylonitrile butadiene rubber (NBR) seal GN 741.5

Information

Fluid fill / drain plugs GN 742.5 can be used in particularly aggressive environments thanks to the material used.

The seal is embedded in a radial recess and thus cannot be lost, squeezed out or overloaded during tightening.

The outer diameter d_1 of the fluid fill / drain plugs GN 742.5 is matched to screw-in holes for pipe fittings according to DIN 3852.

see also...

- [Fluid Fill / Drain Plugs GN 741 / GN 742 \(Aluminum\)](#) → page QVX / QVX
- [Threaded Plugs GN 749 \(Steel, Zinc Plated\)](#) → page QVX
- [Fluid Drain Plugs EN 740 \(Plastic\)](#) → page QVX
- [Fluid Fill Plugs EN 747 \(Plastic\)](#) → page QVX
- [Threaded Plugs GN 442 \(Aluminum, with Finger Grip\)](#) → page QVX

How to order

GN GN 742.5-40-M33X1.5-A-1

- 1** Diameter d_1
- 2** Pipe thread d_2 (Fine thread d_2)
- 3** Type
- 4** Identification no.