



SS Stainless Steel

3 Type

- D With tapped hole
- E With threaded stud

Metric table

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
16 0.63	M 5	M 6	10 0.39	18 0.71	10 0.39	7 0.28
20 0.79	M 6	M 8	12 0.47	24 0.94	12 0.47	9 0.35
25 0.98	M 6	M 8	14 0.55	29 1.14	14 0.55	9 0.35
32 1.26	M 8	M 10	18 0.71	37 1.46	16 0.63	12 0.47
36 1.42	M 10	M 12	20 0.79	42 1.65	18 0.71	15 0.59

Dimensions in: millimeters - inches

* Not available from stock, requires a minimum order quantity

Specification

- **GN 75**
Steel
 - Fine turned
 - Blackened finish
 - Machined from solid bar

- **GN 75.5**
Stainless steel AISI 304
 - Matte shot-blasted finish
 - Highly polished finish

MT
PL*

• [Stainless Steel Characteristics](#) → page 2143

• [RoHS compliant](#)

On request

- Steel, zinc plated
- Stainless steel A4 quality

Information

GN 75 waist shaped knobs are widely used on push / pull type applications. The smooth shape gives the operator a comfortable grip.

GN 75.5 waist shaped knobs are made of high-grade stainless steel, which makes them the first choice when it comes to applications requiring high standards of hygiene. The design of these knobs prevents the collection of moisture and dirt.

see also...

- [Push / Pull Knobs GN 676.1 \(Steel, Blackened Finish\)](#) → page 77
- [Push / Pull Knobs GN 676.5 \(Stainless Steel\)](#) → page 77

How to order (Steel)	1 Handle diameter d ₁
1 2 3 GN 75-25-M6-D	2 Thread d ₂ (Threaded stud d ₃)
	3 Type

How to order (Stainless steel)	1 Handle diameter d ₁
1 2 3 4 GN 75.5-25-M8-E-MT	2 Threaded stud d ₃ (Thread d ₂)
	3 Type
	4 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4