



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁ H9 Bore	² d ₂ Thread	d ₃	d ₄	Length l	r	s -0.2	t min.	w min.
6 0.24	M 6	10 0.39	14 0.55	22 0.87	8.5 0.33	6 0.24	12 0.47	218°
8 0.31	M 8	14 0.55	18 0.71	29 1.14	12 0.47	8 0.31	16 0.63	218°
10 0.39	M 10	18 0.71	23 0.91	35 1.38	14 0.55	10 0.39	20 0.79	212°
12 0.47	M 12	20 0.79	27 1.06	43 1.69	17 0.67	12 0.47	24 0.94	216°
14 0.55	M 14	24 0.94	30 1.18	50 1.97	19 0.75	14 0.55	28 1.10	214°
16 0.63	M 16	26 1.02	36 1.42	56 2.20	22 0.87	16 0.63	32 1.26	216°

Specification

- Steel —
- Property class 5
- Zinc plated, blue passivated finish
- Stainless steel AISI 303 **NI**
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 752 joint ends are designed to be used in combination with GN 751 clevis fork joints.
 see also...
 • Eye Nuts GN 444.2 → www.jwwinco.com
 • Clevis Fork Joints GN 751 → starting from page 1744

How to order (Steel) ¹ ² GN 752-10-M10	1 Bore d ₁
	2 Thread d ₂
How to order (Stainless steel) ¹ ² ³ GN 752-14-M14-NI	1 Bore d ₁
	2 Thread d ₂
	3 Material