



- 3 Type**
- D** With tapped hole
 - E** With threaded stud

Metric table

Dimensions in: millimeters - *inches*

1 d_1	2 d_2 Type D	2 d_3 Type E	d_4	d_5	h	Length l	t min.
20 <i>0.79</i>	M 5	M 5	14 <i>0.55</i>	14.8 <i>0.58</i>	24 <i>0.94</i>	10 <i>0.39</i>	7 <i>0.28</i>
25 <i>0.98</i>	M 6	M 6	16 <i>0.63</i>	16.8 <i>0.66</i>	29 <i>1.14</i>	12 <i>0.47</i>	9 <i>0.35</i>
32 <i>1.26</i>	M 8	M 8	18 <i>0.71</i>	18.8 <i>0.74</i>	37 <i>1.46</i>	14 <i>0.55</i>	12 <i>0.47</i>

Specification

- Stainless steel AISI 316L
 - Matte finish ($R_a < 0.8 \mu m$) **MT**
 - Polished finish ($R_a < 0.8 \mu m$) **PL**
- Sealing ring
 - H-NBR **H**
Temperature resistant from -13 °F to +302 °F (-25 °C to +150 °C)
 - EPDM **E**
Temperature resistant from -40 °F to +248 °F (-40 °C to +120 °C)
 - Blue
 - Hardness 85±5 shore A
 - FDA compliant
- [Stainless Steel Characteristics](#)
- [Elastomer Characteristics](#)
- [RoHS compliant](#)

Accessory

- Sealing rings GN 7600

Information

GN 75.6 waist shaped knobs are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

GN 75.6 waist shaped knobs have a compact and timeless design.

see also...

- [Product Family Hygienic Design](#)

How to order

GN 75.6-25-M6-E-MT-H

- | | |
|----------|--|
| 1 | Handle diameter d_1 |
| 2 | Tapped hole d_2 (Threaded stud d_3) |
| 3 | Type |
| 4 | Finish |
| 5 | Sealing ring material |