



3 Type

- D With tapped insert
- E With threaded stud

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
17 0.67	M 5	M 5	10 0.39	14 0.55	9 0.35	7 0.28
21 0.83	M 6	M 6	12 0.47	17 0.67	10 0.39	11 0.43
25 0.98	M 6	M 6	14 0.55	21 0.83	10 0.39	11 0.43
33 1.30	M 8	M 8	18 0.71	29 1.14	14 0.55	12 0.47

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Tapped insert (Type D)
Brass
- Threaded stud (Type E)
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

GN 76 waist shaped knobs are widely used on push-pull type applications. The smooth shape gives the operator a comfortable grip.

see also...

- *Knurled Knobs EN 676 (Technopolymer Plastic, with Tapped Insert)* → page 73
- *Knurled Knobs EN 676 (Technopolymer Plastic, with Threaded Stud)* → page 76

How to order

GN 76-25-M6-D

- 1** Handle diameter d₁
- 2** Thread d₂ (Threaded stud d₃)
- 3** Type