



Metric table

Dimensions in: millimeters - inches

d ₁	l ₁ ±1						a	b	d ₂	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
28 1.10	300 11.81	400 15.75	500 19.69	600 23.62	700 27.56	-	62.5 2.46	28 1.10	10.5 0.41	54 2.13	68 2.68	20 0.79	26 1.02	19.5 0.77	20.3 0.80
35 1.38	300 11.81	400 15.75	500 19.69	600 23.62	700 27.56	1000 39.37	74 2.91	35 1.38	10.5 0.41	67.5 2.66	85 3.35	28 1.10	24.5 0.96	28.5 1.12	18.5 0.73

Specification

- Tube Ø 35x2 mm
Aluminum
 - **EN 767**
Powder coated
Graphite black, metal effect, matte finish
 - **EN 767.1**
Anodized, natural color
- This information applies to both series:
- End caps
 - Technopolymer (Polyamide PA), shiny finish:
 - Black-gray, RAL 7021
 - Orange, RAL 2004
 - Gray, RAL 7035
 - Yellow, RAL 1021
 - Blue, RAL 5024
 - Red, RAL 3000
 - Green, RAL 6017
 - End pieces
 - Plastic
 - Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 212 °F (100 °C)
 - Black-gray, similar to RAL 7021, matte finish
 - Plastic Characteristics → page QVX
 - RoHS compliant

Information

EN 767 and EN 767.1 tubular handles are highly resistant to wear, scratches and chemical agents. Avoid continuous and prolonged contact with boiling water or steam. Handle legs resistant to solvents, oils, greases and other chemical agents.

Special expansion-assembly system between tube and handle legs prevents rotation during operations. The mechanisms (screws / nuts / clamps) are shrouded by the removable end caps. On assembly the two end caps are inserted from above. To remove the end caps, a flat screw driver should be inserted in the provided recess to pry them out of their location. End caps are available in the different Ergostyle® colors which offers additional possibilities for a variety of color schemes.

see also...

- Product Family Ergostyle® → page QVX
- Tubular Grip Handles GN 667 (Mounting from the Operator's Side) → page QVX

On request

- Tube, end pieces and end caps in white (WS)

How to order (Powder coated tube)	1 Handle diameter d ₁
EN 767-35-700-DSG	2 Length l ₁
	3 Color of the end cap

How to order (Anodized tube)	1 Handle diameter d ₁
EN 767.1-35-500-DSG	2 Length l ₁
	3 Color of the end cap