



- 2 Type**
- A Straight connection
 - B 45° connection
 - C 90° connection

Metric table

1 Size	d ₁ Connection thread for GN 880	3 Hose length l			d ₂ Hose connector	d ₃ Nominal hose width	d ₄ ≈
		250	500	1000			
22	M 22 x 1.5	9.84	19.69	39.37	15 0.59	14 0.55	15.5 0.61
26	M 26 x 1.5	9.84	19.69	39.37	20 0.79	19 0.75	20 0.79

Dimensions in: millimeters - inches

Specification

- Connecting nut with hose connector
Brass
- 45° / 90° connector elbow
Copper
- O-ring
Rubber NBR (Perbunan®)
- Drain hose
PVC, transparent **T**
- Hose clip
Steel, zinc plated
- Plugs
Plastic, PE-LD
- *Elastomer Characteristics* → page 2135
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- Other hose lengths
- Drain hose with fabric inlay (Nylon)

Information

GN 880.1 connector pieces are used in connection with GN 880 fluid drain valves. Screwing on the connector piece actuates the valve plate of the fluid drain valve, allowing the fluid to flow through the hose into a pan. The plug prevents the leakage of residual fluid after emptying. The plugs and the hose clip (only type B and C) are included as part of the order.

see also...

- *Fluid Drain Valves GN 880* → page 1688

How to order (Without drain hose)	1 Size
	2 Type
GN 880.1-26-C	
How to order (With drain hose)	1 Size
	2 Type
	3 Hose length l
	4 Hose version
GN 880.1-22-A-500-T	

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10