









T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Hinges GN 127 → page 1404					
	GN 127-...-B-...	-		GN 965-8-M6-20-B	
Flat Mounting Plates GN 139.3 (for Hinges with / without Integrated Safety Switch GN 139.1 / GN 139.2) → page 1426					
	GN 139.3-170	GN 965-6-M6-12-A		GN 965-8-M6-14-A	
Angled Mounting Plates GN 139.4 (for Hinges with / without Integrated Safety Switch GN 139.1 / GN 139.2) → page 1426					
	GN 139.4-101	GN 965-6-M6-12-A		GN 965-8-M6-14-A	
Flanged Connector Clamps GN 145 → page 1778					
	GN 145-...	-		GN 965-8-M5-16-A	
Hinges EN 151.4 → page 1406					
	EN 151.4-...	-		GN 965-8-M6-18-A	
Hinges EN 159 → page 1356					
	EN 159-54-17-17-... EN 159-74-22-22-...	GN 965-6-M6-16-B -		- GN 965-8-M6-18-B	



T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Double Hinges EN 159.1 → www.jwwinco.com					
	EN 159.1-89-35-... EN 159.1-119-45-...	GN 965-6-M6-16-B -		- GN 965-8-M6-18-B	
Hinges GN 161 → www.jwwinco.com					
	GN 161-57 GN 161-68 GN 161-80	-		GN 965-8-M6-16-B	
Base Plate Connector Clamps GN 162.3 → page 1786					
	GN 162.3-...	GN 965-6-M5-16-A		GN 965-8-M5-18-A	
Base Plate Mounting Clamps EN 175 → page XYZ					
	EN 175-B10-... EN 175-B12-... EN 175-B14-...	GN 965-6-M6-12-A		GN 965-8-M6-14-A	
Mounting Plate Sets GN 181 (for Cabinet “U” Handles) → page 103					
	GN 181-ZD-8-M4-... GN 181-ZD-10-M5-... GN 181-ZD-...-M6-... GN 181-ZD-...-M8-...	GN 965-6-M4-10-B GN 965-6-M5-12-B GN 965-6-M6-12-B -		- GN 965-8-M5-14-B GN 965-8-M6-14-B GN 965-8-M8-16-B	
Tube Supports GN 231 → page 1797					
	GN 231-B20 / -B25 / -B30-... GN 231-V20 / -V25 / -V30-...	-		GN 965-8-M8-14-A	
Hinges EN 236 → www.jwwinco.com					
	EN 236-75-60	-		GN 965-8-M6-20-B	





T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Hinges without Switch EN 239.3 → page 1434					
	EN 239.3-70-60-SH	-	-	GN 965-8-M6-18-B	
Hinges with Integrated Switch EN 239.4 → page 1434					
	EN 239.4-...	-	-	GN 965-8-M6-18-B	
Hinges with Integrated Safety Switch EN 239.6 → page 1430					
	EN 239.6-60-110-...	-	-	GN 965-8-M6-18-B	
Hinges without Switch EN 239.7 → page 1430					
	EN 239.7-60-70 EN 239.7-60-110	-	-	GN 965-8-M6-18-B	
Flat Mounting Plates EN 239.8 (for Hinges with / without Integrated Safety Switch EN 239.6 / EN 239.7) → page 1432					
	EN 239.8-110-14 EN 239.8-110-19	GN 965-6-M6-16-B -	-	GN 965-8-M6-18-B	
Swivel Clamp Connector Bases GN 271 → www.jwwinco.com					
	GN 271-25-...	-	-	GN 965-8-M5-18-A	
Sensor Brackets GN 271.4 → www.jwwinco.com					
	GN 271.4-B12-... GN 271.4-B18-...	-	-	GN 965-8-M5-18-A	



T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Swivel Clamp Connector Joints GN 281 → page 1799					
	GN 281-...	-		GN 965-8-M5-18-A	
Tubular Handles GN 333 → page 168					
	GN 333-28-...-B-...	GN 965-6-M6-25-A		GN 965-8-M6-28-A	
Tubular Handles GN 333.1 → page 164					
	GN 333.1-28-...-B-...	GN 965-6-M6-14-C		GN 965-8-M6-16-C	
Oval Tubular Handles GN 334.1 → page 175					
	GN 334.1-36-...	-		GN 965-8-M8-16-C	
Oval Tubular Handles GN 335 → page 176					
	GN 335-36-...-B-...	-		GN 965-8-M8-16-C	
Indexing Plungers GN 412 → page 974					
	GN 412-5-35-...-1 GN 412-6-35-...-1 GN 412-8-47-...-1 GN 412-10-47-...-1	GN 965-6-M4-16-A GN 965-6-M4-16-A GN 965-6-M5-18-A GN 965-6-M5-18-A		- - GN 965-8-M5-20-A GN 965-8-M5-20-A	
Mounting Blocks GN 412.1 → page 998					
	GN 412.1-35-...-1 GN 412.1-47-...-1	GN 965-6-M4-16-A GN 965-6-M5-18-A		- GN 965-8-M5-20-A	





T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Indexing Plunger Latch Mechanisms GN 416 → page 975					
	GN 416-6-38-... GN 416-8-38-... GN 416-8-46-... GN 416-10-38-... GN 416-10-46-... GN 416-12-46-...	GN 965-6-M5-14-A GN 965-6-M5-14-A - GN 965-6-M5-14-A - -	GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A GN 965-8-M6-16-A		
Locators GN 416.1 → www.jwwinco.com					
	GN 416.1-6-38 GN 416.1-8-38 GN 416.1-8-46 GN 416.1-10-38 GN 416.1-10-46 GN 416.1-12-46	GN 965-6-M5-14-A GN 965-6-M5-14-A - GN 965-6-M5-14-A - -	GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A GN 965-8-M6-16-A		
Indexing Plunger Latch Mechanisms GN 417 → page 976 / 977					
	GN 417-5-A / -B / -C GN 417-6-A / -B / -C GN 417-8-A / -B GN 417-8-C GN 417-10-A / -B / -C	GN 965-6-M4-12-A GN 965-6-M5-14-A GN 965-6-M5-14-A - -	- GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A		
Locators GN 417.1 → www.jwwinco.com					
	GN 417.1-5-ST-SW GN 417.1-6-ST-SW GN 417.1-8-ST-SW GN 417.1-10-ST-SW	GN 965-6-M4-12-A GN 965-6-M5-14-A GN 965-6-M5-14-A -	- GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A		
Locators GN 417.1 → www.jwwinco.com					
	GN 417.1-5-NI-GS GN 417.1-6-NI-GS GN 417.1-8-NI-GS GN 417.1-10-NI-GS	GN 965-6-M4-12-A GN 965-6-M5-14-A GN 965-6-M5-14-A -	- GN 965-8-M5-16-A GN 965-8-M5-16-A GN 965-8-M6-16-A		
Snap Door Latches EN 449.1 → page 1304					
	EN 449.1-57-...	GN 965-6-M6-14-A	GN 965-8-M6-16-A		
Base Plate Mounting Clamps GN 473 → page 1819					
	GN 473-B8-... GN 473-B10 / -B12-... GN 473-B15 / -B16-... GN 473-B20-...	GN 965-6-M4-10-A - - -	GN 965-8-M4-14-A GN 965-8-M5-12-A GN 965-8-M6-14-A GN 965-8-M6-18-A		

T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Mounting Clamps GN 477 → page 1820					
	GN 477-B8-... GN 477-B10 / -B12-... GN 477-B15 / -B16 / -B20-...	GN 965-6-M4-16-A GN 965-6-M5-18-A GN 965-6-M6-20-A		GN 965-8-M4-20-A GN 965-8-M5-20-A GN 965-8-M6-22-A	
Flanged Mounting Bolts GN 480 → page 1828					
	GN 480-8-... GN 480-10 / -12-... GN 480-15 / -16 / -20-...	GN 965-6-M4-10-A GN 965-6-M5-10-A GN 965-6-M6-12-A		GN 965-8-M4-12-A GN 965-8-M5-12-A GN 965-8-M6-14-A	
Cabinet “U” Handles EN 528 → page 114					
	EN 528-...-94-6.5-... EN 528-...-117-6.5-.. EN 528-...-117-8.5-... EN 528-...-132-8.5-... EN 528-...-140-8.5-... EN 528-...-160-8.5-... EN 528-...-179-8.5-...	GN 965-6-M6-14-A GN 965-6-M6-16-A - - - - -		GN 965-8-M6-16-A GN 965-8-M6-16-A GN 965-8-M8-18-A GN 965-8-M8-18-A GN 965-8-M8-18-A GN 965-8-M8-20-A GN 965-8-M8-20-A	
Mounting Angle Brackets EN 561 → www.jwwinco.com					
	EN 561-19-... EN 561-25-...	-		GN 965-8-M8-18-C	
Cabinet “U” Handles GN 565.1 → page 99					
	GN 565.1-20-... GN 565.1-26-...	GN 965-6-M5-22-A -		- GN 965-8-M6-22-A	
Angled Cabinet “U” Handles GN 565.2 → page 106					
	GN 565.2-26-128-B-... GN 565.2-26-160-B-...	- -		GN 965-8-M6-22-C GN 965-8-M6-22-C	
Cam Action Indexing Plungers GN 612.2 → page 1010					
	GN 612.2-...-16-... GN 612.2-...-20-...	GN 965-6-M5-18-A GN 965-6-M5-22-A		GN 965-8-M5-22-A GN 965-8-M5-25-A	



T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Cam Action Indexing Plungers GN 612.9 → page 1011					
	GN 612.9-...-16-... GN 612.9-...-20-...	GN 965-6-M5-18-A GN 965-6-M5-22-A	GN 965-8-M5-20-A GN 965-8-M5-25-A		
Bridge Handles EN 628 → page 130					
	EN 628-117-6.5-B-... EN 628-117-8.5-B-... EN 628-150-8.5-B-... EN 628-179-8.5-B-...	GN 965-6-M6-16-A - - -	- GN 965-8-M8-28-A GN 965-8-M8-28-A GN 965-8-M8-28-A		
Off-Set Enclosed Safety “U” Handles EN 630 → page 194					
	EN 630-114-B-...	GN 965-6-M6-18-B	GN 965-8-M6-22-C		
Off-Set Open „U“ Handles EN 630.1 → page 108					
	EN 630.1-114-B-...	GN 965-6-M6-18-B	GN 965-8-M6-22-C		
Panel Support Clamps EN 649 → www.jwwinco.com					
	EN 649-35-E	GN 965-6-M6-10-D	GN 965-8-M6-14-D		
Tubular Grip Handles GN 667 → page 172					
	GN 667-20-...	-	GN 965-8-M8-20-A		
Square Cam Action Spring Latches GN 722.3 → page 1012					
	GN 722.3-8-... GN 722.3-10-... GN 722.3-12-... GN 722.3-14-...	-	GN 965-8-M6-18-A		

T-Nut Assemblies GN 965		Type A	Type B	Type C	Type D
					
Compatible GN series sorted by series number					
Economical Cabinet “U” Handles GN 728 → page 120					
	GN 728-120-B-... GN 728-180-B-...	GN 965-6-M6-14-A -	- GN 965-8-M8-18-A		
Economical Cabinet “U” Handles GN 728.5 → page 120					
	GN 728.5-120-B	GN 965-6-M6-14-A	-		
Slam Latches / Slam Locks GN 936 → page 1302					
	GN 936-72-...	GN 965-6-M6-12-A	GN 965-8-M6-14-A		
Connecting Brackets GN 967 → www.jwwinco.com					
	GN 967-...-20-...-1-... GN 967-...-20-...-2-... GN 967-...-30-...-1-... GN 967-...-30-...-2-... GN 967-...-40-...-1-... GN 967-...-40-...-2-... GN 967-...-45-...-1-... GN 967-...-45-...-2-...	GN 965-6-M5-12-A GN 965-6-M5-12-B GN 965-6-M6-12-A GN 965-6-M6-12-B - - - -	GN 965-8-M5-14-A GN 965-8-M5-14-B GN 965-8-M6-14-A GN 965-8-M6-14-B GN 965-8-M8-16-A GN 965-8-M8-16-B GN 965-8-M8-16-A GN 965-8-M8-16-B		
Threaded Flanges GN 3490 → www.jwwinco.com					
	GN 3490-45-... GN 3490-60-...	GN 965-6-M6-14-B -	- GN 965-8-M8-16-B		
Ball Catches GN 4490 → page 1305					
	GN 4490-ZD-50... GN 4490-ZD-68... GN 4490-ZD-80...	GN 965-6-M4-10-B GN 965-6-M4-10-B GN 965-6-M5-14-B	GN 965-8-M4-12-B GN 965-8-M4-12-B GN 965-8-M5-14-B		

