



Inch table

Dimensions in: inches - millimeters

d ₁	d ₂ Thread										t ₁
.75 19.1	10 x 32	10 x 24	-	-	-	-	-	-	-	-	.38 9.7
1.00 25.4	10 x 32	10 x 24	-	-	-	-	-	-	-	-	.38 9.7
1.00 25.4	1/4 x 20	1/4 x 28	5/16 x 18	5/16 x 24	3/8 x 16	-	-	-	-	-	.50 12.7
1.38 35.1	1/4 x 20	1/4 x 28	5/16 x 18	3/8 x 16	3/8 x 24	5/16 x 24	7/16 x 20	1/2 x 13	1/2 x 20	-	.63 16.0
1.88 47.8	3/8 x 16	3/8 x 24	5/8 x 11	1/2 x 13	1/2 x 20	5/8 x 18	-	-	-	-	.75 19.1

Specification

- Steel
Highly polished
- Brass
- Highly polished
- Corrosion resistant in water
- Tapped hole for mounting
- RoHS compliant



Information

BK ball knobs are highly polished and turned from a solid bar stock. They are used on fixtures, machine tools, jigs and assemblies.
 see also...
 • Ball Knobs DIN 319 (Metric, Steel, Stainless Steel and Aluminum)

How to order

BK-MS-1.00-5/16X18

- 1 **Material**
- 2 **Handle diameter d₁**
- 3 **Thread d₂**

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

