



Inch table



Dimensions in: inches - *millimeters*

d_1 Thread			d_2	d_3	h_1	h_2
10 x 24	10 x 32	1/4 x 20	.75 19.1	.50 12.7	.22 5.6	.16 4.1
5/16 x 18	3/8 x 16	-	.75 19.1	.50 12.7	.31 7.9	.25 6.4
1/2 x 13	5/8 x 11	-	1.00 25.4	.75 19.1	.38 9.7	.25 6.4

Specification

- Low carbon steel, black oxide finish
- RoHS compliant

Information

CN check nuts may be used in combination with other components such as knurled head screws, torque thumb screws, hand knob assemblies, toggle shoe clamp assemblies and many other tooling applications.

see also...

- Swivel Clamp Screws TS

<p>How to order</p> <p>CN-10X24</p>	<p>1 Thread d_1</p>
--	----------------------------------